

KERN OBB-A 1261

KERN

Planachromatic objective 40x /0,65 (0,72 mm) (sprung)



Pictograms

STANDARD



Category

| | |
|------------------|----------------------|
| Brand | Optics |
| Product category | Optical Instrument |
| Product group | Microscope objective |

Construction

| | |
|-------------|---|
| Anti fungus | ✓ |
|-------------|---|

Objective

| | |
|----------------------------|-----------------|
| Objective magnification | 40x |
| Objective quality | Plan achromatic |
| Numerical Aperture | 0,65 |
| Objective working distance | 0,72 mm |

Environmental conditions

| | |
|---------------------------|-------|
| Storage temperature [Min] | -5 °C |
| Storage temperature [Max] | 40 °C |

Packing & Shipping

| | |
|------------------------------|----------------|
| Delivery time | 1 d |
| Dimensions packaging (W×D×H) | 65×40×40 mm |
| Shipping method | Parcel service |
| Net weight approx. | 0,30 kg |
| Gross weight approx. | 0,60 kg |
| Shipping weight | 0,6 kg |

Product information

| | |
|----------------------|--------------------------|
| GTIN/EAN number | 4045761167964 |
| Trade number | 90119000 |
| REACH classification | no prohibited substances |