

# KERN OBE 101

# KERN

The fully equipped all-round compound microscope for school, training and laboratories



## Category

Brand	Optics
Product category	Microscope
Product group	Compound microscope
Product family	OBE-10

## Construction

Dimension (WxDxH)	320x180x365 mm
Optical system	Finite
Tube type	Monocular
Tube angle of inclination	30°
Tube 360° rotation	✓

Contrasting methods	Bright field Darkfield (optional) Polarisation (optional)
---------------------	---

Standard objectives	4x 10x 40x
---------------------	------------------

Lens quality	achromatic
Nosepiece screw-in locations	4
Eyepieces fixed	✓
Colour temperature	6000 K

## Ocular

Ocular type	Eyepiece HWF 10 x / Ø 18mm with anti-fungus, high eye point
Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10 x
Ocular visual field	18 mm
Ocular diameter	23,2 mm

## Objective

Objectives - Details	Objective Achromatic 10 x / 0,25 anti-fungus Objective Achromatic 4 x / 0,1 anti-fungus Objective Achromatic 40 x / 0,65 spring, anti-fungus
Objectives magnifications	4 x / 10 x / 40 x

## Illumination

Illuminance	Transmitted light
Illumination type incident light	none
Illumination type transmitted light	LED
Illumination intensity transmitted light	3 W
Filter possible	✓
Aperture diaphragm	✓

## Focussing

Field of view [Min]	0,18 mm
Field of view [Max]	4,5 mm
Torque regulation	✓
Fine drive minimum	0,002 mm
Focusing mechanism	coaxial coarse and fine drive

## Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Built-in power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	AUS UK US CH
Input voltage power supply / power [Max]	100 - 240 V
Input voltage device / power [Max]	100 - 240 V

## Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

## Approval

CE mark	✓
---------	---

# KERN OBE 101



The fully equipped all-round compound microscope for school, training and laboratories

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	425×340×245 mm
Shipping method	Parcel service
Net weight approx.	4,6 kg
Gross weight approx.	6 kg
Shipping weight	7,1 kg

## Pictograms

### STANDARD



### OPTION

