

KERN OBE 124C832

KERN

Our all-round compound microscope as a comprehensive digital solution for schools, training and laboratories



Category

Brand	Optics
Product category	Microscope
Product group	Digital microscope set
Product family	OBE-S

Construction

Dimension (W×D×H)	360×150×390 mm
Optical system	Finite
Tube type	Trinocular
Tube angle of inclination	30°
Tube 360° rotation	✓
Tube type	Butterfly
Light distribution	20:80 0:100

Contrasting methods
Bright field
Darkfield (optional)

Standard objectives	4× 10× 40×
Lens quality	achromatic
Nosepiece screw-in locations	4
Eyepieces fixed	✓
Interpupillary distance [Min]	50 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	one-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5
Colour temperature	6000 K

Functions

Camera - Applicable software	Microscope VIS 2.0 Pro (OXM 902)
------------------------------	-------------------------------------

Supported operating systems	Win XP
	Win Vista
	Win 7
	Win 8
	Win 10

Interface

Interfaces	USB 3.0
------------	---------

Ocular

Ocular field width	HWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	18 mm
Ocular diameter	23,2 mm

Illumination

Illuminance	Transmitted light
Illumination type transmitted light	LED
Illumination intensity transmitted light	3 W
Illumination dimmable	Transmitted light
Filter possible	✓

Focussing

Field of view [Min]	0,18 mm
Field of view [Max]	4,5 mm
Torque regulation	✓
Fine drive minimum	0,002 mm
Focusing mechanism	coaxial coarse and fine drive

Condensor

Condensor type	Abbe
----------------	------

Camera

Cameratype	USB3 Microscope camera - C-Mount
Camera - Resolution	5,1 MP
Camera - Sensor type	CMOS
Camera - Sensor size	1/2,5"
Camera - Colour depth	Colour
Camera - Framerate	14,2 - 101,2 fps
Camera- Mounting types	C-mount thread
Camera - Exposure method	Rolling Shutter

KERN OBE 124C832



Our all-round compound microscope as a comprehensive digital solution for schools, training and laboratories

Power Supply

Supplied power supply	Power supply unit
-----------------------	-------------------

Power supply type	Power adapter
-------------------	---------------

Plug-in power supply / adapter for countries - included with the delivery	EURO
---	------

Plug-in power supply / adapter for countries - optional	AUS
	UK
	US
	CH

Input voltage power supply / power [Max]	100 - 240 V
--	-------------

Power supply cable removable	removable
------------------------------	-----------

Input voltage device / power [Max]	5 V, 1 A
------------------------------------	----------

Environmental conditions

Storage temperature [Min]	-5 °C
---------------------------	-------

Storage temperature [Max]	40 °C
---------------------------	-------

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	560×440×330 mm
------------------------------	----------------

Shipping method	Parcel service
-----------------	----------------

Net weight approx.	6 kg
--------------------	------

Gross weight approx.	8 kg
----------------------	------

Shipping weight	16,3 kg
-----------------	---------

Product information

GTIN/EAN number	4045761356764
-----------------	---------------

Trade number	90118000
--------------	----------

REACH classification	no prohibited substances
----------------------	--------------------------

Pictograms

STANDARD



OPTION

