

KERN ORF1PM

Area of application: Urine



Measuring system

Accuracy:	0.0003 nD0 001 sgU0 1 g/dl
ATC:	yes
Division:	0.0001 nD0 001 sgU0 1 g/dl
Measuring capacity:	1.3330 nD - 1 3990 nD1 000 sgU - 1 050 sgU0 g/dl - 12 g/dl
Scales:	Refractive indexUrine (spec. gravity)Serum proteine

Power supply

Battery:	2x1.5 V AAA
----------	-------------

Services (optional)

Factory calibration certificate:	961-290
----------------------------------	---------

Category

Brand:	Optics
--------	--------

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	235 x 200 x 65 mm
Gross weight:	650 g
Net weight:	558,210 g
Shipping method:	Parcel service

Construction

Dimensions (WxDxH):	145 x 67 x 40 mm
---------------------	------------------

Piktogramme

STANDARD

