

# KERN OZO 556

# KERN

Individuality, variety and flexible working through our modular construction system ▶ Stereo microscope heads



Field of view [Max]	3,3 mm
Standard total magnification [Min]	8x
Standard total magnification [Max]	70x
Zoom [Min]	0,8x
Zoom [Max]	7x
Working distance	108 mm
Magnification ratio	8,8:1

## Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

## Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	310×300×220 mm
Shipping method	Parcel service
Net weight approx.	2,6 kg
Gross weight approx.	3,0 kg
Shipping weight	4,1 kg

## Product information

GTIN/EAN number	4045761183629
Trade number	90119000
REACH classification	no prohibited substances

## Pictograms

### STANDARD



## Category

Brand	Optics
Product category	Microscope
Product group	Stereo Microscope-Head
Product family	OZB-M

## Construction

Optical system	Greenough
Tube type	Binocular
Tube angle of inclination	35°
Tube 360° rotation	✓
Interpupillary distance [Min]	52 mm
Interpupillary distance [Max]	76 mm
Diopter adjustment	both-sided
Diopter adjustment [Min]	-6
Diopter adjustment [Max]	6

## Ocular

Ocular type	Eyepiece HSWF 10x / Ø 23mm with anti-fungus, high eye point
Ocular field width	HSWF
Eye point	High Eye Point
Ocular magnifications	10x
Ocular visual field	23 mm
Ocular diameter	30 mm

## Objective

Objectives magnifications	0,8x - 7x
---------------------------	-----------

## Focussing

Field of view [Min]	28,75 mm
---------------------	----------