

MAGNETIC TIP

PG_VMAG | 4 SKUs, 4 LENGTHS

PG_VMAG

The magnetic hook end sticks to attach to any metal surface. Stick it to a metal door frame and you can pace off 10 feet or more. Great for drop ceiling work, steel framing, HVAC, and shop work.

FEATURES

- Magnetic Tip** holds fast to metal attachment points.
- Nylon-Coating** extends life of the blade.
- High-Impact, High Visibility, Keson-Orange ABS Case** with rubber grip protects the blade and stands up to heavy use.



A: 5/8-inch wide, nylon-coated, short tape



A9 = SAE: ft., in., 1/8, 1/16 (1/32 in. first ft.)

B: 1-inch wide, nylon-coated, short tape



B9 = SAE: ft., in., 1/8, 1/16 (1/32 in. first ft.)



B10 = SAE/M: ft., in., 1/8, 1/16 & cm, mm

PRODUCT FEATURES & BENEFITS

Lock	Slide or Button release					
Case	Chrome-coated ABS/High visibility orange ABS		Rubber grip/High visibility			
Blade	Nylon-coated steel					
Impact Durability	High-visibility rubber grip		Holds up to accidental drops			
MODEL	UPC 052837	LENGTH	UNITS	WIDTH (IN)	STAND OUT (FT)	BLADE*
PG1816ALVMAG	028702	16 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	5/8"	up to 8'	A9
PG1825VMAG	027828	25 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1"	up to 8'	B9
PG18M26VMAG	028726	26 ft.	ft, in, 1/8, 1/16 & cm, mm	1"	up to 8'	B10
PG1835VMAG	028733	35 ft.	ft, in, 1/8, 1/16 (1/32 first 12")	1"	up to 8'	B9

See Pages 70-71

ECONOMY SERIES

PG_ | 2 SKUs, 1 LENGTH

PG_

The co-molded plastic housing holds a lacquer-coated blade with easy to read marking of each eight, quarter and half inch. A side brake will slow or stop the blade return when engaged. A good tape at a very reasonable price.

FEATURES

- Side Brake** slows or stops the blade return when engaged.
- Lacquer Coated** blade.
- High-Impact, High-Visibility, ABS Case** with rubber grip protects the blade and stands up to heavy use.



B: 1-inch wide, lacquer-coated, short tape



B2 = ENG: ft., 1/10, 1/100



B8 = SAE, ft., in., 1/8, 1/16 with fractions

PRODUCT FEATURES & BENEFITS

Lock	Slide					
Case	High-impact, high-visibility ABS with rubber grip					
MODEL	UPC 052837	LENGTH	UNITS	WIDTH (IN)	STAND OUT (FT)	BLADE*
PG25	022076	25 ft.	ft, in, 1/8, 1/16 with fractions	1"	up to 8'	B8
PG2510	026371	25 ft.	ft, 1/10, 1/100	1"	up to 8'	B2

See Pages 70-71