

PLASTIC WHEEL MODEL SUMMARY



PLASTIC MEASURING WHEELS

Innovative wheels make measuring quick and easy. Balanced and lightweight, and extremely durable.

MODEL	UPC 052837	UNITS	DIA.	CIRC.	SPECIAL	WARRANTY
RRT6	027422	ft. & in.	6 in.	18 in.	Handle trigger reset and brake	2 Yr. Limited
RRT610	027576	ft. & 10ths	6 in.	18 in.		
RRT6M	027569	m, dm	15.2 cm	45.7 cm		
RRT12	027415	ft. & in.	12 in.	3 ft.	Handle trigger reset and brake	2 Yr. Limited
RRT1210	027460	ft. & 10ths	12 in.	3 ft.		
RRT12M	027477	m, dm	.318 m	1 m		
RR30	026425	ft., in.	11-1/2 in.	3 ft.	Increased strength & weight	Limited Lifetime
RR3010	026524	ft., 10ths	11-1/2 in.	3 ft.		
RR30M	026500	m, dm	.318 m	1 m		
RR40	026463	ft., in.	15-1/2 in.	4 ft.	Best seller	Limited Lifetime
RR318N	008506	ft., in.	12-1/2 in.	3 ft.		
RR318N-2	008506	ft., in.	12-1/2 in.	3 ft.		
RR310	010172	ft., 10ths	12-1/2 in.	3 ft.		Limited Lifetime
RR3M	010189	m, dm	.318 m	1 m		
RR418	010196	ft., in.	15-1/2 in.	4 ft.	Great for rough terrain	
RR410	010202	ft., 10ths	15-1/2 in.	4 ft.	Great for rough terrain	Limited Lifetime
RR112	020058	ft., in.	4 in.	1 ft.	Best seller	
RR110	020065	ft., 10ths	4 in.	1 ft.		
RR10M	020072	m, dm	.097 m	.305 m		Limited Lifetime
RR182	010592	ft., in.	4 in.	1 ft.	Dual-wheel stability	
RR102	010608	ft., 10ths	4 in.	1 ft.	Dual-wheel stability	Limited Lifetime
RRPA18	022298	ft. & in.	4 in.	1 ft.	Single wheel & applicator	
RRPA182	020768	ft. & in.	4 in.	1 ft.	Dual wheel & applicator	

All wheels are molded, assembled, and tested in USA except RRT series.