



AFDF-125 - 1-1/4" Hub, ZA12 zinc alloy Expansion and Deflection Combination Fittings

By Killark
Catalog # [AFDF-125](#)

1-1/4" Hub, ZA12 zinc alloy Expansion and Deflection Combination Fittings

Features

- AF Conduit body is casted from durable and natural corrosive resistant ZA12 zinc alloy
- Includes type "A" phenolic insulating bushing
- PTFE Teflon reinforced gasket with steel washer to help maintain a superior seal
- Between the AF/DF is malleable, ductile iron or steel nipple
- DF end couplings are casted with a ZA12 zinc alloy with standard tapered threads for rigid or IMC conduit
- Silicone Rubber sleeve for high UV and environmentally corrosion resistance
- Tinned braided copper grounding straps for electrical continuity
- Rain, water and concretetight
- Includes tinned braided copper external bonding jumper (AJE Series)



Specifications

EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Hub Size	1-1/4"
----------	--------

General

Type	Expansion/Deflection
Series	AFDF Series
Material	Zinc Alloy, ZA12
Finish Type	Natural
UPC	783936156583

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)