



AFDF-50 - 1/2" Hub, ZA12 zinc alloy Expansion and Deflection Combination Fittings

By Killark
Catalog # [AFDF-50](#)

1/2" Hub, ZA12 zinc alloy Expansion and Deflection Combination
Fittings

Features

- AF Conduit body is casted from durable and natural corrosive resistant ZA12 zinc alloy
- Includes type "A" phenolic insulating bushing
- PTFE Teflon reinforced gasket with steel washer to help maintain a superior seal
- Between the AF/DF is malleable, ductile iron or steel nipple
- DF end couplings are casted with a ZA12 zinc alloy with standard tapered threads for rigid or IMC conduit
- Silicone Rubber sleeve for high UV and environmentally corrosion resistance
- Tinned braided copper grounding straps for electrical continuity
- Rain, water and concretetight
- Includes tinned braided copper external bonding jumper (AJE Series)



Specifications

EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Hub Size	1/2"
----------	------

General

Type	Expansion/Deflection
Series	AFDF Series
Material	Zinc Alloy, ZA12
Finish Type	Natural
UPC	783936155692

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)