



CGB112NB - CGB Series - Unarmored Cable Connector 1/2" NPT Nickel Plated Brass

By Killark
Catalog # [CGB112NB](#)

CGB Series - Unarmored Cable Connector 1/2" NPT Nickel Plated Brass

Features

- Revolutionary design covers a broader range of cable sizes
- Grommet sleeves are field removable to adjust to multiple cable ranges and cable diameter variances
- Eliminates carrying numerous amounts of different CGB type connectors for job sites
- Available in sizes ranging from 1/2" to 4" NPT in copper-free aluminum, zinc plated steel, 316L stainless steel and nickel plated brass finishes.

Application

Suitable for use in Class I Divisions 2 when installed in accordance to NEC 501.10(B)(4). Approved for cable use including TC, TC-ER, TC-ER-HL, PLTC, PLTC-ER, ITC, ITC-HL and cords including S, SO, STO, ST, SJ, SJT, SJTO, SVO.

Conductor

Cable Range .12 - .354 in



Dimensions

Hub Size	1/2"
Width	0.96 in
Weight	0.15 lb.
Height	1.7 in

General

Series	CGB Series
Finish Name	Natural
Material	Nickel Plated Brass
UPC	783936180243
Ingress Protection	Type 3R, 4, 4X, 12

Operational

Operating Temperature	- 40C to +80 °C
-----------------------	-----------------

Product Assets

[Catalog \[English\]](#)



A Hubbell brand