



# DVL1630X2G - DVL Series LED Dust Tight / Utility Hazardous Rated 16 Watt, 120-277 VAC 5000K, 1355 Lumens

By Killark  
Catalog # [DVL1630X2G](#)

DVL Series LED Dust Tight/ Utility Hazardous Rated 16 Watt, 120-277 VAC 5000K, 1355 Lumens

## Features

- Compact in Size with Traditional Industrial Appearance and Suitability
- DVL LED Housings can be retrofitted to existing DV Series splice boxes to upgrade from incandescent housing 100 Series components
- World Voltage 120 - 277VAC 50/60Hz
- Instant On - Including after power interruption
- Solder-LESS LED Board Connections - Vibration Resistant
- LM80-08 Measurement of lumen maintenance for LED light sources
- LM79-08 Certified "Absolute" Photometry, including Chromaticity Color for Solid State Lighting
- L70 Values - Industry Nomenclature for Hours of use to 70% of Initial Lumens (TM-21+ Cal.)

## Specifications

|                          |                                                                                                                                                                                  |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s)      | <ul style="list-style-type: none"><li>• Class I, Division 2, Groups A, B, C, D</li><li>• Class II, Division 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| EU RoHS Indicator        | Contact Manufacturer                                                                                                                                                             |
| Buy America(n) Qualified | Contact Manufacturer                                                                                                                                                             |

## Current

|                  |             |
|------------------|-------------|
| Frequency Rating | 50/60 Hz    |
| Lumens Per Watt  | 84.7        |
| Wattage          | 16 W        |
| Voltage Rating   | 120-277 VAC |

## Dimensions

|          |      |
|----------|------|
| Hub Size | 3/4" |
|----------|------|

## General

|               |                                              |
|---------------|----------------------------------------------|
| Series        | DVL Series                                   |
| Material      | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type   | Powder Epoxy Paint                           |
| Optic Type    | Glass Globe - Clear                          |
| UPC           | 783936084176                                 |
| Light Source  | LED                                          |
| Mounting Type | Ceiling                                      |

## Operational

|             |            |
|-------------|------------|
| Lumens      | 1355       |
| Lumen Range | 0-2,000 lm |

## Product Assets

[Catalog \[English\]](#)

