



# EBSEL1030A2 - EBS 10W/30V DC EL 3/4" Pendant

By Killark  
Catalog # [EBSEL1030A2](#)

EBS 10W/30V DC EL 3/4" Pendant

## Features

- LED Heads provide clear crisp illumination at 5000° Kelvin
- LED Head L70 value 100,000 hours for minimal maintenance
- Two head models up to 500% brighter than competitive conventional units
- Enclosure Type 4 (NEMA 4) for wet and harsh locations
- Group B is standard when using EBSHK type heads
- Automatic Safety Disconnect – Removing main cover disconnects battery power
- Ambient Suitability 0°C to 45°C Battery Unit Heads to 55°
- Compact unit requires only two mounting points
- World Voltage 120-277 VAC 50/60Hz input Other Features
- High % of lumens maintained during 90 minute egress cycle
- EBSHK type heads are fully adjustable on unit or remote when ordered with RFSL Factory Sealed mounting kits
- EBSEL type heads are factory sealed on their EZ type mounting boxes
- Heads can be remote mounted over 300' from battery unit
- Ni-Cad sealed batteries provide 90 minutes of illumination
- Integral base unit LED pilot light indicates AC power is present
- Choice of Integral or Remote Push-To-Test station to verify system operation
- Vapor Capsule to inhibit corrosion is standard with main enclosure unit
- Terminal Blocks identified for incoming and outgoing connections

## Specifications

- |                     |                                                                                                                                                 |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li></ul> |
|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|



- Class II, Divisions 1 & 2, Groups E, F, G
  - Class III, Divisions 1 & 2
- Contact Manufacturer  
Contact Manufacturer

EU RoHS Indicator  
Buy America(n) Qualified

## Current

|                  |             |
|------------------|-------------|
| Frequency Rating | 50/60 Hz    |
| Lumens Per Watt  | 108.1       |
| Wattage          | 10 W        |
| Voltage Rating   | 120-277 VAC |

## Dimensions

|          |      |
|----------|------|
| Hub Size | 3/4" |
|----------|------|

## General

|               |                                              |
|---------------|----------------------------------------------|
| Series        | EBS Series                                   |
| Material      | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type   | Powder Epoxy Paint                           |
| Optic Type    | Glass Globe - Clear                          |
| UPC           | 783936083124                                 |
| Light Source  | LED                                          |
| Mounting Type | Pendant                                      |

## Operational

|             |            |
|-------------|------------|
| Lumens      | 1081       |
| Lumen Range | 0-2,000 lm |

## Product Assets

[Catalog \[English\]](#)



A Hubbell brand