



ECF-115 - 1/2" Flexible Coupling with 15" Bend Length, Bronze

By Killark
Catalog # [ECF-115](#)

1/2" Flexible Coupling with 15" Bend Length, Bronze



Features

- Bronze flexible metal construction
- An inner liner of asphaltum impregnated jute fibre tubing to protect conductors
- Female ends with removable zinc plated steel nipples standard on all couplings
- Union type couplings may be assembled by adding a GUF Series union to the nipple
- Special lengths available-consult factory

Application

For use in hazardous areas where movement or vibration requires a flexible connection or a difficult bend is required in a conduit system.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups A, B, C, D • Class I, Zones 1 & 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	---

EU RoHS Indicator	Contact Manufacturer
UL File Number	E10514
CSA File Number	LR11716
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Gross Weight with Packaging	2.41
Hub Size	1/2"
Width	2.375 in
Height	2.5 in
Length	20.5 in
Dimensions	20.5 in x 2.375 in x 2.5 in

General

Type	Flexible Coupling
Series	ECF Series
Material	Bronze
Finish Type	Natural
UPC	783936105031
Color	Bronze

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)