



EEQ3232E30A2 - EEQ Emergency CFL 32N32E 120/277V Pendant

By Killark
Catalog # [EEQ3232E30A2](#)

EEQ Emergency CFL 32N32E 120/277V Pendant

Features

- Quad-Pin long-life triple-tube compact
- Fluorescent lamps included
- Choice of Pendant, Ceiling, Wall or Stanchion mount
- Factory Sealed - No external seal required
- Corrosion resistant-Copper-free aluminum (less than 4/10 of 1%) die-cast construction w/Baked-on epoxy/polyester powder finish Exposed hardware is 316 grade stainless steel
- LED charging indicator light visible through lens

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current



Frequency Rating	50/60 Hz
Wattage	32 W
Voltage Rating	120-277 VAC

Dimensions

Hub Size	3/4"
----------	------

General

Series	EEQ Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Lamp Type	Quad Pin
Optic Type	Glass Globe - Clear
UPC	783936960050
Light Source	Compact Fluorescent
Mounting Type	Pendant

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)