



EKJ-24 - 3/4" Flexible Coupling with 4" Bend Length, Bronze

By Killark
Catalog # [EKJ-24](#)

3/4" Flexible Coupling with 4" Bend Length, Bronze



Features

- Bronze flexible metal construction
- An inner liner of asphaltum impregnated jute fibre tubing to protect conductors
- Female ends with removable zinc plated steel nipples standard on all couplings
- Union type couplings may be assembled by adding a GUF Series union to the nipple
- Special lengths available-consult factory
- Furnished with a setscrew (for use as a fixture hanging coupling)

Application

For use in hazardous areas where movement or vibration requires a flexible connection or a difficult bend is required in a conduit system.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups A, B, C, D • Class I, Zones 1 & 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G
---------------------	--

EU RoHS Indicator	• Class III, Divisions 1 & 2
UL File Number	Contact Manufacturer
CSA File Number	E10514
Buy America(n) Qualified	LR11716
	Contact Manufacturer

Dimensions

Gross Weight with Packaging	2.5
Hub Size	3/4"
Width	1.62 in
Height	1.62 in
Length	8.75 in
Dimensions	8.75 in x 1.62 in x 1.62 in

General

Type	Flexible Coupling
Series	EKJ Series
Material	Bronze
Finish Type	Natural
UPC	783936107462
Color	Bronze

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)