



EKJ-324 - 1" x 24" Flexible Coupling, Bronze

By Killark
Catalog # [EKJ-324](#)

1" x 24" Flexible Coupling, Bronze



Features

- Bronze flexible metal construction
- An inner liner of asphaltum impregnated jute fibre tubing to protect conductors
- Female ends with removable zinc plated steel nipples standard on all couplings
- Union type couplings may be assembled by adding a GUF Series union to the nipple
- Special lengths available-consult factory
- Furnished with a setscrew (for use as a fixture hanging coupling)

Application

For use in hazardous areas where movement or vibration requires a flexible connection or a difficult bend is required in a conduit system.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups A, B, C, D • Class I, Zones 1 & 2, Groups IIC, IIB, IIA
---------------------	--

EU RoHS Indicator
UL File Number
CSA File Number
Buy America(n) Qualified

- Class II, Divisions 1 & 2, Groups E, F, G
 - Class III, Divisions 1 & 2
- Contact Manufacturer
E10514
LR11716
Contact Manufacturer

Dimensions

Gross Weight with Packaging	11.8
Hub Size	1"

General

Type	Flexible Coupling
Series	EKJ Series
Material	Bronze
Finish Type	Natural
UPC	783936014036
Color	Bronze

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)