



EKJUF-615 - 2" Flexible Coupling with 15" Bend Length, Bronze

By Killark
Catalog # [EKJUF-615](#)

2" Flexible Coupling with 15" Bend Length, Bronze



Features

- Bronze flexible metal construction
- An inner liner of asphaltum impregnated jute fibre tubing to protect conductors
- Provided with one zinc plated steel nipple and one zinc plated steel female union
- Special lengths available – consult factory

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups A, B, C, D • Class I, Zones 1 & 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
UL File Number	E10514
CSA File Number	LR11716

Buy America(n) Qualified Contact Manufacturer

Dimensions

Hub Size 2"

General

Type	Flexible Coupling With Female Union
Series	EKJUF Series
Material	Bronze
Finish Type	Natural
UPC	783936106021

Logistics

Carton Quantity 1

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)