



EMI15B2G SU104

By Killark
Catalog # EMI15B2G SU104

Class I 150W Incandescent 3/4" Pendant with Guard- Unit Pack.



Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

General

Finish Type	Peinture époxy en poudre
Lamp Type	Medium Base
Light Source	Incandescent
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Wall Bracket
Optic Type	Glass Globe - Fluted
Series	EM
UPC	783936028019

Dimensions

Hub Size	3/4"
----------	------

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120-277 VAC
Wattage	150 W

Certifications and Compliance

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	--

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Photometry - KIL_EMI15-S](#)
[Photometry - KIL_EMI15-A](#)
[Photometry - KIL_EMI15](#)



A proud member of the Hubbell Family.