



EMI15X2 - Incandescent 150W 3/4" Ceiling Mount

By Killark
Catalog # [EMI15X2](#)

Incandescent 150W 3/4" Ceiling Mount

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

General

Catalog Number	EMI15X2
EU RoHS Indicator	Contact Manufacturer
Finish Type	Powder Epoxy Paint
Lamp Type	Medium Base
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Optic Type	Glass Globe - Fluted
Series	EM
UPC	783936145389

Dimensions



Hub Size 3/4"

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	120-277 VAC
Wattage	150 W

Certifications And Compliance

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	--

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Photometry - KIL_EMI15](#)
- [Photometry - KIL_EMI15-A](#)
- [Photometry - KIL_EMI15-S](#)
- [Specifications - EM-EQ Series Specification Sheet](#)
- [Specifications - EMI15X2 Specification Sheet French](#)
- [Specifications - EMI15X2 Specification Sheet English](#)