



# EMI30D4 - Incandescent 2/300W 1-1/4" Stanchion Mount with Guard

By Killark  
Catalog # EMI30D4

Incandescent 2/300W 1-1/4" Stanchion Mount with Guard

## Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

## Specifications

|                     |                                                                                                                                                                                                                                                  |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|



EU RoHS Indicator

Contact Manufacturer

## Current

|                  |             |
|------------------|-------------|
| Frequency Rating | 60 Hz       |
| Voltage Rating   | 120-277 VAC |
| Wattage          | 300 W       |

## Dimensions

|          |        |
|----------|--------|
| Hub Size | 1-1/4" |
|----------|--------|

## General

|               |                                              |
|---------------|----------------------------------------------|
| Optic Type    | Glass Globe - Fluted                         |
| Lamp Type     | Medium Base                                  |
| Mounting Type | Stanchion 25°                                |
| UPC           | 783936135038                                 |
| Light Source  | Incandescent                                 |
| Material      | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type   | Powder Epoxy Paint                           |
| Series        | EM Series                                    |

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|