



EMI30D4G - Incandescent 2/300W 1-1/4" Stanchion Mount with Guard

By Killark
Catalog # EMI30D4G

Incandescent 2/300W 1-1/4" Stanchion Mount with Guard

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	--



EU RoHS Indicator	Contact Manufacturer
Current	
Frequency Rating	60 Hz
Voltage Rating	120-277 VAC
Wattage	300 W
Dimensions	
Hub Size	1-1/4"
General	
Optic Type	Glass Globe - Fluted
Lamp Type	Medium Base
Mounting Type	Stanchion 25°
UPC	783936148076
Light Source	Incandescent
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Series	EM Series
Logistics	
Carton Quantity	1