

KILL

EMS070B2 - HID 70W HPS Quadri-Volt 3/4" Wall Mount

By Killark

Catalog # [EMS070B2](#)

HID 70W HPS Quadri-Volt 3/4" Wall Mount



Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

Specifications

Hazardous Rating(s)

- Class I, Divisions 1 & 2, Groups C, D
- Class I, Zones 1 & 2, Groups IIB, IIA
- Class II, Divisions 1 & 2, Groups E, F, G
- Class III, Divisions 1 & 2

EU RoHS Indicator
Contact Manufacturer

Current

Frequency Rating
60 Hz
Voltage Rating
Quad - 120/277/347/480 VAC
Wattage
70 W

Dimensions

Hub Size
3/4"

General

Optic Type
Glass Globe - Fluted
Lamp Type
Medium Base
Mounting Type
Wall Bracket
UPC
783936135991
Light Source
High Pressure Sodium
Material
Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type
Powder Epoxy Paint
Series
EM Series



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
KILL_CA-EMS070B2-SPEC-EN | REV 5/2026