



# EMS151B2 - HID 150W Fluorescent 120V HPS 3/4" Wall Mount

By Killark  
Catalog # EMS151B2

HID 150W Fluorescent 120V HPS 3/4" Wall Mount

## Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction.
- Baked powder epoxy finish, electrostatically applied.
- Exposed hardware is 316 grade stainless steel.

## Specifications

|                     |                                             |
|---------------------|---------------------------------------------|
| Hazardous Rating(s) | • Class I, Divisions 1 & 2, Groups C, D     |
|                     | • Class I, Zones 1 & 2, Groups IIB, IIA     |
|                     | • Class II, Divisions 1 & 2, Groups E, F, G |



EU RoHS Indicator

- Class III, Divisions 1 & 2  
Contact Manufacturer

## Current

|                  |         |
|------------------|---------|
| Frequency Rating | 60 Hz   |
| Voltage Rating   | 120 VAC |
| Wattage          | 150 W   |

## Dimensions

|          |      |
|----------|------|
| Hub Size | 3/4" |
|----------|------|

## General

|               |                                              |
|---------------|----------------------------------------------|
| Optic Type    | Glass Globe - Fluted                         |
| Lamp Type     | Medium Base                                  |
| Mounting Type | Wall Bracket                                 |
| UPC           | 783936136318                                 |
| Light Source  | High Pressure Sodium                         |
| Material      | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type   | Powder Epoxy Paint                           |
| Series        | EM Series                                    |