



ENY Series

By Killark
Catalog # [ENY-7-T](#)

ENY Seal Fitting Aluminum, Male/Female



Features

- Minimal turn radius for optimal spacing of both enclosures and conduit
- Large openings for ease of access to conductors for proper dam installation
- Engineered to latest 419 hub specifications for superior continuity and ingress protection
- integral bushings to protect conductors during installation

Application

To minimize the passage of gases and vapors from one electrical installation to another through the conduit system. To confine any explosions from sealed enclosures and prevent pressure pilling between conduit systems.

Specifications

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups C, DClass II, Divisions 1 & 2, Groups E, F, GClass III, Divisions 1 & 2
---------------------	--

Nema Rating	3R
UL File Number	E10514

Dimensions

Turning Radius	3.1
Hub Size	2-1/2"
Width	3.34 in
Weight	3.08 lb.
Height	8.01 in

General

Type	Sealing Fitting
Series	ENY Series
Material	Copper-free aluminum (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
UPC	783936186689
Color	Gray

Logistics

Carton Quantity	1
-----------------	---