



EQF2630X2 - 26W Fluorescent 120-277V 3/4" Ceiling Mount Fixture

By Killark
Catalog # [EQF2630X2](#)

26W Fluorescent 120-277V 3/4" Ceiling Mount Fixture

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction. Baked powder epoxy finish, electrostatically applied. Exposed hardware is 316 grade stainless steel.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer



Buy America(n) Qualified	Contact Manufacturer
Current	
Frequency Rating	50/60 Hz
Wattage	26 W
Voltage Rating	120-277 VAC
Dimensions	
Hub Size	3/4"
General	
Series	EQF Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Lamp Type	Quad Pin
Optic Type	Glass Globe - Clear
UPC	783936028460
Light Source	Compact Fluorescent
Mounting Type	Ceiling
Product Assets	
Catalog [English]	