



# EQF4219 - EQF Series - 42W Fluorescent 120VDC Housing and Globe Luminaire

By Killark  
Catalog # [EQF4219](#)

EQF Series - 42W Fluorescent 120VDC Housing and Globe Luminaire

## Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction. Baked powder epoxy finish, electrostatically applied. Exposed hardware is 316 grade stainless steel.

## Specifications

|                     |                                             |
|---------------------|---------------------------------------------|
| Hazardous Rating(s) | • Class I, Divisions 1 & 2, Groups C, D     |
|                     | • Class I, Zones 1 & 2, Groups IIB, IIA     |
|                     | • Class II, Divisions 1 & 2, Groups E, F, G |



EU RoHS Indicator  
Buy America(n) Qualified

• Class III, Divisions 1 & 2  
Contact Manufacturer  
Contact Manufacturer

## Current

|                |         |
|----------------|---------|
| Wattage        | 42 W    |
| Voltage Rating | 120 VDC |

## General

|              |                                              |
|--------------|----------------------------------------------|
| Series       | EQF Series                                   |
| Material     | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type  | Powder Epoxy Paint                           |
| Lamp Type    | Quad Pin                                     |
| Optic Type   | Glass Globe - Clear                          |
| UPC          | 783936103792                                 |
| Light Source | Compact Fluorescent                          |

## Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)