



# EQF4230D4G - 42W Fluorescent 120-277V 1-1/4" Stanchion Mount with Guard

By Killark  
Catalog # [EQF4230D4G](#)

42W Fluorescent 120-277V 1-1/4" Stanchion Mount with Guard

## Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction. Baked powder epoxy finish, electrostatically applied. Exposed hardware is 316 grade stainless steel.

## Specifications

|                     |                                                                                                                                                                                                                                                  |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Groups C, D</li><li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| EU RoHS Indicator   | Contact Manufacturer                                                                                                                                                                                                                             |



Buy America(n) Qualified      Contact Manufacturer

## Current

|                  |             |
|------------------|-------------|
| Frequency Rating | 50/60 Hz    |
| Wattage          | 42 W        |
| Voltage Rating   | 120-277 VAC |

## Dimensions

|          |        |
|----------|--------|
| Hub Size | 1-1/4" |
|----------|--------|

## General

|               |                                              |
|---------------|----------------------------------------------|
| Series        | EQF Series                                   |
| Material      | Aluminum, Copper Free (less than 4/10 of 1%) |
| Finish Type   | Powder Epoxy Paint                           |
| Lamp Type     | Quad Pin                                     |
| Optic Type    | Glass Globe - Clear                          |
| UPC           | 783936143521                                 |
| Light Source  | Compact Fluorescent                          |
| Mounting Type | Stanchion 25°                                |

## Product Assets

[Catalog \[English\]](#)