



EQF8419 - 84W Fluorescent 120VDC HSG/Globe Luminaire

By Killark
Catalog # EQF8419

84W Fluorescent 120VDC HSG/Globe Luminaire

Features

- Four light sources—Incandescent, compact fluorescent, high pressure sodium and metal halide
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation
- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Compact size—Medium base incandescent and HID lamps, plus PL fluorescent lamps allow smaller fixture design
- Corrosion resistant—Copper-free aluminum die-cast construction. Baked powder epoxy finish, electrostatically applied. Exposed hardware is 316 grade stainless steel.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D
	• Class I, Zones 1 & 2, Groups IIB, IIA
	• Class II, Divisions 1 & 2, Groups E, F, G



EU RoHS Indicator
Buy America(n) Qualified

• Class III, Divisions 1 & 2
Contact Manufacturer
Contact Manufacturer

Current

Wattage	84 W
Voltage Rating	120 VDC

General

Series	EQF Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Lamp Type	Quad Pin
Optic Type	Glass Globe - Clear
UPC	783936103815
Light Source	Compact Fluorescent

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)