



EMI15/20/EBF



EMI30 & HID



Pendant



Ceiling



Wall Bracket



25° Stanchion

UL Listed - Files E10514 and E91793 (Marine)
SP Certified - File LR11713

Housing, Globe and Globe Support Assemblies^①

INCANDESCENT			
CATALOG NUMBER	LAMP TYPE	WATTS	VOLTS ^③
EMI15	A-19	60, 75	250 MAX. VAC
	A-19, A-21	100	
	A-21	150	
EMI20	A-23, PS-25	150	250 MAX. VAC
	A-23, PS-25	200	
	PS-25	300	
EMI30	PS-25	200	250 MAX. VAC
	PS-30	300	

FLUORESCENT with lamp(s)*			
CATALOG NUMBER	ANSI LAMP TYPE	WATTS	VOLTS
EBF131	Bi-Pin	13	120VAC
EBF134	Fluorescent		277VAC
EBF261	Bi-Pin	26 (2x13)	120VAC
EBF264	Fluorescent		277VAC
EQF2630	Quad Pin Fluorescent	26	120-277 VAC 50-60Hz
EQF3230		32	
EQF4230		42	
EQF5230		52 (2X26)	
EQF6430		64 (2X32)	
EQF8430		84 (2X42)	

HPS			
CATALOG NUMBER	ANSI LAMP TYPE	WATTS	VOLTS @60HZ.
EMS351	S-76	35	120
EMS050	S-68	50	Quadri-Volt
EMS070	S-62	70	Quadri-Volt
EMS075			480
EMS100	S-54	100	Quadri-Volt
EMS105			480
EMS151	S-55	150	120

METAL HALIDE			
CATALOG NUMBER	ANSI LAMP TYPE	WATTS	VOLTS @60HZ.
EMH050	M-110	50	Quadri-Volt
EMH070	M-98	70	Quadri-Volt
EMH100	M-90	100	Quadri-Volt

MOUNTING BOXES				
CATALOG NUMBER				HUB SIZE
PENDANT	CEILING	BRACKET	STANCHION	
EZA2	EZX2	EZB2	—	3/4"
EZA3	EZX3	EZB3	—	1"
—	—	—	EZD4*	1-1/4"/1-1/2"

*1-1/2" furnished with 1-1/2"-1-1/4" reducer



HIC-BEIGE
replacement
wiring plug
for EZBx
Wall Bracket



EZCUP

Close up plug for
EZ mounting
boxes. Used for
maintenance when
fixture is removed
for service.



EMG1



EMG2



EAC®



Standard Dome



Angle Dome

GUARDS		
CATALOG NUMBER	SERIES	LAMP TYPE
EMG1	EMI15	INC
	EMI20	INC
	EBF	Bi-Pin
	EQF (26, 32, 42)	Quad-Pin
EMG2	EMI30	INC
	EMS	HPS
	EMH	MH
	ESX	Strobe
	EQF (52, 64, 84)	Quad-Pin

Guards are cast of copper-free aluminum with electrostatically applied epoxy/polyester finish.

① Assemblies may be ordered with the CEN (CENELEC) suffix. See page L144 for more information.

② Adapters for discontinued Killark "H" Series and Crouse Hinds® available. See page L224 for more information.

③ UL fixture rating; socket rated 600V.

* Consult factory for 52, 64 and 84 Watt availability.

REFLECTORS		
CATALOG NUMBER		SERIES
STANDARD DOME	ANGLE	
ERSD15	ERA15	EMI15/EMI20
		EBF
		EQF
ERSD30	ERA30	EMI30
		EMS
		EMH
		EQF (52, 64, 84)

Reflectors are aluminum with white finish.



FACTORY SEALED

Class I, DIV. 1 BCD
Class II, DIV. 1 & 2 EFG
CLASS III
NEMA 3, 4X IP66
*40°C ambient T3 Rated

PHOTO CELL FIELD KITS WITH HKB-GL BOX AND COVER

CATALOG NUMBER	VOLTS
VMHKPC1	120VAC
VMHKPC2	208-277VAC
VMHKPC3	347VAC



KILLARK®