

LIGHTING

EBS SERIES



EMERGENCY BATTERY SYSTEM – REMOTE HEADS & ACCESSORIES



EBSSEL
Shown with
Exit Accessory

EBSSEL1030 REMOTE HEADS WITH MOUNT (FACTORY SEALED)				CID1CD; C2D1EFG	
10W 30VDC	PENDANT 3/4"①	CEILING 3/4"①	WALL 3/4"①	STANCHION 1-1/2"②	
With Guard	EBSSEL1030A2G	EBSSEL1030X2G	EBSSEL1030B2G	EBSSEL1030D4G	
Without Guard③	EBSSEL1030A2	EBSSEL1030X2	EBSSEL1030B2	EBSSEL1030D4	

EBSSEL1030 COMPONENTS & ACCESSORIES – DESCRIPTION	CATALOG NUMBER
EBSSEL 10W 30V Head Only with LED's, Less Mount and Guard	EBSSEL1030
Guard	EMG1
Red Guard – used to signify remote fixture is for Emergency	EMG1-R③
EXIT Accessory – 3-sided white painted aluminum	HEXA-100③
Dome Reflector	ERSD15
Angle Reflector	ERA15
Sealed Fittings Set for attachment of Pendant EBSSEL to EBS23HD-xxx	EBS-AHFS
Replacement Globe and Support Assembly	EMGS1



EBSSEL1030



EMG1



EMG1-R



ERSD15



ERA15



EMGS1



MOUNTING BOXES				
CATALOG NUMBER				HUB SIZE
PENDANT	CEILING	BRACKET	STANCHION	
EZA2	EZX2	EZB2	-	3/4"
EZA3	EZX3	EZB3	-	1"
-	-	-	EZD4②	1-1/4" / 1-1/2"

① For 1" pendant, ceiling and wall hubs, substitute "3" for "2" in catalog number; example: EBSSEL1030A3G.

② Stanchion conduit hub size supplied is 1-1/2" with 1-1/2" to 1-1/4" reducer for 1-1/4" mounting.

③ Order fixture without guard for use with HEXA-100 EXIT Accessory, or to order EMG1-R Red Guard.

④ For EBSSEL with Mount Dimensions, see EMI15 series in lighting section.

EBSHK1030 10W 30V HEADS, COMPONENTS & ACCESSORIES		CID1BCD; C2D1EFG	
DESCRIPTION	CATALOG NUMBER		
EBSHK Head Only with LED's – Requires Field Seal①	EBSHK1030		
EBSHK Head with ADJUSTABLE FACTORY SEALED "C" fittings set	EBSHK1030-RFSC		
EBSHK Head with ADJUSTABLE FACTORY SEALED "L" fittings set	EBSHK1030-RFSL		
Sealed Fittings Set for attachment of EBSHK to EBS23DH-xxx	EBS-AHFS		

① Seal purchased separately appropriate of area of use

EBS23DH SERIES ACCESSORIES – DESCRIPTION	CATALOG NUMBER
Remote Push-To-Test Station Group B 3/4" Feed-Thru w/Close Up Plug①	EBS-PTT
Remote Push-To-Test Station with Lock Off, Group B 3/4" Feed-Thru①	EBS-PTT-LO
Lock-Off for Integral Push-To-Test	G010502
Sealed Fittings Set for attachment of EBSHK to GEBC-2 or GEBL-2	EBS-AHFS
Replacement Battery Pack and Electronics	KLBP01
Replacement Vapor Capsule for corrosion protection	EBS-VC

① EBS23DH requires conduit seals (purchased separately) exiting enclosure within 18"; EBS-PTT contains a N.C. contact and is Factory Sealed for C&D and up to 5' for Group B.



EBSHK1030



EBSHK1030-RFSL



EBSHK1030-RFSC



EBS-PTT



COMPONENT PARTS/ACCESSORIES



EMI15/20/EBF



EMI30 & HID



Pendant



Ceiling



Wall Bracket



25° Stanchion

UL LISTED - Files E10514 and E91793 (Marine)
SP Certified - File LR11713

Housing, Globe and Globe Support Assemblies^①

INCANDESCENT			
CATALOG NUMBER	LAMP TYPE	WATTS	VOLTS ^③
EMI15	A-19	60, 75	250 MAX. VAC
	A-19, A-21	100	
	A-21	150	
EMI20	A-23, PS-25	150	250 MAX. VAC
	A-23, PS-25	200	
	PS-25	300	
EMI30	PS-25	200	250 MAX. VAC
	PS-30	300	

FLUORESCENT WITH LAMP(S)*			
CATALOG NUMBER	ANSI LAMP TYPE	WATTS	VOLTS
EQF2630	Quad Pin Fluorescent	26	120-277 VAC 50-60Hz
EQF3230		32	
EQF4230		42	
EQF5230		52 (2X26)	
EQF6430		64 (2X32)	
EQF8430		84 (2X42)	

HPS			
CATALOG NUMBER	ANSI LAMP TYPE	WATTS	VOLTS @60HZ
EMS351	S-76	35	120
EMS050	S-68	50	Quad
EMS070	S-62	70	Quad
EMS075			480
EMS100	S-54	100	Quad
EMS105			480
EMS151			120

METAL HALIDE			
CATALOG NUMBER	ANSI LAMP TYPE	WATTS	VOLTS @60HZ
EMH050	M-110	50	Quadri-Volt
EMH070	M-98	70	Quadri-Volt
EMH100	M-90	100	Quadri-Volt

MOUNTING BOXES				
CATALOG NUMBER				HUB SIZE
PENDANT	CEILING	BRACKET	STANCHION	
EZA2	EZX2	EZB2	—	3/4"
EZA3	EZX3	EZB3	—	1"
—	—	—	EZD4*	1-1/4"/1-1/2"*

*1-1/2" furnished with 1-1/2"-1-1/4" reducer



HIC-BEIGE
replacement wiring plug for EZBx Wall Bracket



Close up plug for EZ mounting boxes. Used for maintenance when fixture is removed for service.



EMG1



EMG2



EACK



Standard Dome



Angle Dome

GUARDS		
CATALOG NUMBER	SERIES	LAMP TYPE
EMG1	EMI15	INC
	EMI20	INC
	EQF (26, 32, 42)	Quad-Pin
EMG2	EMI30	INC
	EMS	HPS
	EMH	MH
	ESX	Strobe
EQF (52, 64, 84)	Quad-Pin	

Guards are cast of copper-free aluminum with electrostatically applied epoxy/polyester finish.

- * Consult factory for 52, 64 and 84 Watt availability.
- ① Assemblies may be ordered with the CEN (CENELEC) suffix. See page L148 for more information.
- ② Adapters for discontinued Killark "H" Series and Crouse Hinds® available.
- ③ UL fixture rating; socket rated 600V.

REFLECTORS		
CATALOG NUMBER		SERIES
STANDARD DOME	ANGLE	
ERSD15	ERA15	EMI15/EMI20
		EQF
ERSD30	ERA30	EMI30
		EMS
		EMH
		EQF (52, 64, 84)

Reflectors are aluminum with white finish.



FACTORY SEALED

Class I, DIV. 1 BCD
 Class II, DIV. 1&2 EFG
CLASS III
 NEMA 3, 4X IP66
 *40°C ambient T3 Rated

PHOTO CELL FIELD KITS WITH HKB - GL BOX AND COVER

CATALOG NUMBER	VOLTS
VMHKPC1	120VAC
VMHKPC2	208-277VAC
VMHKPC3	347VAC