



EYD-100 - 1" EYD Drain Seal Fitting Aluminum, Female/Female

By Killark
Catalog # [EYD-100](#)

1" EYD Drain Seal Fitting Aluminum, Female/Female

Features

- Threaded for Rigid Conduit or IMC
- Tapered threads (NPT)
- Simple to install.
- Internal drainage path provides a visual means to ensure that the compound chamber is properly filled.
- Large cover openings for easy packing of fiber dam.
- Temporary plastic sleeve protects thread for drain/breather from contamination when pouring compound.
- Unique design enables installation of drain/breather right after compound is poured.
- Provides continuous water drain path while allowing conduit run to breathe, in compliance with the NEC.
- Includes Drain Breather Fitting KDB-375.

Application

Class I, Divisions 1 and 2: The purpose of seals in a Class I hazardous location is to minimize the passage of gases and vapors and prevent the passage of flames from one electrical installation to another through the conduit system. Seals are required to

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups E, F, G
---------------------	---



EU RoHS Indicator	• Class III, Divisions 1 & 2
Buy America(n) Qualified	Contact Manufacturer
Contact Manufacturer	Contact Manufacturer
Dimensions	
Gross Weight with Packaging	0.81
Hub Size	1"
Width	10 in
Height	0.1 in
Length	5 in
Dimensions	5 in x 10 in x 0.1 in
General	
Type	Sealing Fitting
Series	EYD Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
UPC	783936090306
Color	Gray
Logistics	
Carton Quantity	4
Product Assets	
Catalog [English]	
Installation Manual [English]	
Installation Manual [English]	