



EYD-6 - 2" EYD Seal Fitting Aluminum, Female/Female

By Killark
Catalog # [EYD-6](#)



EYD Drain Seal Fitting Aluminum, Female/Female

Features

- Threaded for Rigid Conduit or IMC
- Tapered threads (NPT)
- Simplified installation
- Internal drainage path provides a visual means to ensure that the compound chamber is properly filled
- Temporary plastic sleeve protects thread for drain/breather from contamination when pouring compound
- Unique design enables installation of drain/breather right after compound is poured – no waiting
- Provides continuous water drain path while allowing conduit run to breathe, in compliance with the NEC
- Includes Drain Breather Fitting KDB-1

Application

To minimize the passage of gases and vapors from one electrical installation to another through the conduit system. To confine any explosions from sealed enclosures and prevent pressure pilling between conduit systems.

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11716
Ratings	3R
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class II, Divisions 1 & 2, Groups E, F, G

UL File Number
Buy America(n) Qualified

- Class III, Divisions 1 & 2
- E10514
Contact Manufacturer

Dimensions

Hub Size	2"
Length	5 in
Gross Weight with Packaging	2.1
Turning Radius	2.9
Width	2.9 in
Height	6.4 in
Dimensions	5 in x 2.9 in x 6.4 in

General

Series	EYD Series
Color	Gray
Type	Sealing Fitting
Material	Copper-free aluminum (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
UPC	783936110769

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)