



EYD-8 - 3" EYD Seal Fitting Aluminum, Female/Female

By Killark
Catalog # [EYD-8](#)

EYD Drain Seal Fitting Aluminum, Female/Female



Features

- Threaded for Rigid Conduit or IMC
- Tapered threads (NPT)
- Simplified installation
- Internal drainage path provides a visual means to ensure that the compound chamber is properly filled
- Temporary plastic sleeve protects thread for drain/breather from contamination when pouring compound
- Unique design enables installation of drain/breather right after compound is poured – no waiting
- Provides continuous water drain path while allowing conduit run to breathe, in compliance with the NEC
- Includes Drain Breather Fitting KDB-1

Application

To minimize the passage of gases and vapors from one electrical installation to another through the conduit system. To confine any explosions from sealed enclosures and prevent pressure pilling between conduit systems.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
UL File Number	E10514

CSA File Number	LR11716
Buy America(n) Qualified Ratings	Contact Manufacturer 3R
Dimensions	
Gross Weight with Packaging	4.2
Turning Radius	3.57
Hub Size	3"
Width	4.125 in
Weight	4.28 lb.
Height	8.52 in
General	
Type	Sealing Fitting
Series	EYD Series
Material	Copper-free aluminum (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
UPC	78393618661
Color	Gray

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)