



EYD-9 - 3-1/2" EYD Seal Fitting Aluminum, Female/Female

By Killark
Catalog # [EYD-9](#)

EYD Drain Seal Fitting Aluminum, Female/Female



Features

- Threaded for Rigid Conduit or IMC
- Tapered threads (NPT)
- Simplified installation
- Internal drainage path provides a visual means to ensure that the compound chamber is properly filled
- Temporary plastic sleeve protects thread for drain/breather from contamination when pouring compound
- Unique design enables installation of drain/breather right after compound is poured – no waiting
- Provides continuous water drain path while allowing conduit run to breathe, in compliance with the NEC
- Includes Drain Breather Fitting KDB-1

Application

To minimize the passage of gases and vapors from one electrical installation to another through the conduit system while offering a degree of ventilation and draining of condensation. To confine any explosions from sealed enclosures and prevent pressure pilling between conduit systems.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer

UL File Number	E10514
CSA File Number	LR11716
Buy America(n) Qualified Ratings	Contact Manufacturer 3R

Dimensions

Gross Weight with Packaging	7.2
Turning Radius	3.89
Hub Size	3-1/2"
Width	4.625 in
Weight	5.52 lb.
Height	9.21 in

General

Type	Sealing Fitting
Series	EYD Series
Material	Copper-free aluminum (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
UPC	78393618662
Color	Gray

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)