



SEALING FITTINGS



ENY-1, 2, 3, 4, 5, 6
Class I, Div. 1 & 2, Groups A, B, C, D
Class I, Zone 1, Groups IIC, IIB, IIA
Class II, Div. 1 & 2, Groups E, F, G
Class III

EYS Series
Class I, Div. 1 & 2, Groups C, D
Class I, Zone 1, Groups IIB, IIA
Class II, Div. 1 & 2, Groups E, F, G
Class III

UL LISTED File No. E10514

SP Certified File No. LR11716
See files for details or call Killark.

FEATURES-SPECIFICATIONS

Material/Finish

Copper-free Aluminum
(less than 4/10 of 1%)


- Electrostatically applied powder coating

Duraloy Iron

- Tri-Coat Finish of electrozinc, chromate sealant, and electrostatically applied powder coating

ENY SEALING FITTINGS						ENY WITH NIPPLE	
HUB SIZE	CATALOG NUMBER		DIMENSIONS		TURNING RADIUS	CATALOG NUMBER	
	KILLARK ALUMINUM	DURALOY IRON	A	B		KILLARK ALUMINUM	DURALOY IRON
1/2"	ENY-1	ENY-1M	4-1/16" (103)	1-9/32" (33)	1-3/32" (30)	ENY-1-T	ENY-1TM
3/4"	ENY-2	ENY-2M	4-3/16" (106)	1-1/2" (38)	1-9/32" (33)	ENY-2-T	ENY-2TM
1"	ENY-3	ENY-3M	5" (127)	1-3/4" (45)	1-13/32" (36)	ENY-3-T	ENY-3TM
1-1/4"	ENY-4	ENY-4M	5-3/8" (137)	2-3/16" (56)	1-25/32" (45)	ENY-4-T	ENY-4TM
1-1/2"	ENY-5	ENY-5M	5-11/16" (144)	2-3/8" (60)	1-29/32" (48)	ENY-5-T	ENY-5TM
2"	ENY-6	ENY-6M	6-3/8" (162)	2-3/8" (60)	2-5/16" (59)	ENY-6-T	ENY-6TM

Dimensions



EYS SEALING FITTINGS						EYS WITH NIPPLE	
HUB SIZE	CATALOG NUMBER		DIMENSIONS		TURNING RADIUS	CATALOG NUMBER	
	KILLARK ALUMINUM	DURALOY IRON	A	B		KILLARK ALUMINUM	DURALOY IRON
1/2"	EYS-1	—	2-15/16" (75)	1-13/16" (46)	1-3/16" (30)	EYS-1-T	—
3/4"	EYS-2	—	4-1/16" (103)	2-1/16" (52)	1-9/32" (33)	EYS-2-T	—
1"	EYS-3	—	4-25/32" (121)	2-11/32" (60)	1-13/32" (36)	EYS-3-T	—
1-1/4"	EYS-4	—	5-3/8" (137)	3" (76)	1-25/32" (45)	EYS-4-T	—
1-1/2"	EYS-5	—	5-11/16" (144)	3-1/4" (83)	1-29/32" (48)	EYS-5-T	—
2"	EYS-6	—	6-3/8" (162)	3-15/16" (100)	2-5/16" (59)	EYS-6-T	—
2-1/2"	EYS-7	EYS-7M	7-5/8" (194)	4-1/2" (114)	4-1/8" (105)	EYS-7-T	EYS-7TM
3"	EYS-8	EYS-8M	7-5/8" (194)	4-1/2" (114)	4-3/8" (111)	EYS-8-T	EYS-8TM
3-1/2"	EYS-9	EYS-9M	7-1/8" (181)	5-3/16" (132)	4-3/4" (121)	EYS-9-T	EYS-9TM
4"	EYS-0	EYS-0M	7-1/8" (181)	5-3/16" (132)	4-3/4" (121)	EYS-0-T	EYS-0TM