



EZ2 - EZ Series Vertical Conduit Seal-off with Preinstalled Dam Solution

By Killark
Catalog # [EZ2](#)

EZ Series Vertical Conduit Seal-off with Preinstalled Dam Solution



Features

- Symmetrical and uniform design allows for a quicker installation due to immediate connection to the conduit – no more lining up pouring spouts
- Minimal turn radius offering optimized spacing for both enclosures and conduit
- 360° unimpeded access to potting chamber allowing simplified compound pouring
- Pre-installed disc brush damming technology to drastically reduce packing fiber and installation time
- Retrofittable in case the need to rerun wires occur
- Certified to both fast curing two-part epoxy resin, CELOX, and the traditional SC sealing compound
- Type 3R rated for outdoor applications

Application

Class I, Divisions 1 and 2: The purpose of seals in a Class I hazardous location is to minimize the passage of gases and vapors and prevent the passage of flames from one electrical installation to another through the conduit system

Specifications

Hazardous Rating(s)	Class I, Divisions 1 & 2, Groups A, B, C, DClass II, Divisions 1 & 2, Groups E, F, GClass III, Divisions 1 & 2
---------------------	--

Nema Rating	3R
UL File Number	E10514

Dimensions

Hub Size	3/4"
Width	1.6 in
Weight	0.51 lb.
Height	4.44 in

General

Series	EZ Seal Series
Material	Copper-free aluminum (less than 4/10 of 1%)
Finish Type	Natural
UPC	783936185484

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[English\]](#)