



Housing Globe & Globe Support Assemblies

NOTE: See pages L98-99 for ballast data & fuse kit information.

FEATURES-SPECIFICATIONS

HPS HOUSING GLOBE & GLOBE SUPPORT ASSEMBLIES ^①			
WATTS	ANSI LAMP TYPE	VOLTAGE	CATALOG NUMBER
50	S-68/HPS	120, 208, 240, 277/60Hz	EZS050
		220, 240V/50Hz	EZS058
70	S-62/HPS	120, 208, 240, 277/60Hz	EZS070
		480 60Hz	EZS075
		120, 277, 347/60Hz	EZS076
		220, 240V/50Hz	EZS078
100	S-54/HPS	120, 208, 240, 277/60Hz	EZS100
		480 60Hz	EZS105
		120, 277, 347/60Hz	EZS106
		220, 240V/50Hz	EZS108
150	S-55/HPS	120, 208, 240, 277/60Hz	EZS150
		480 60Hz	EZS155
		120, 277, 347/60Hz	EZS156
		220, 240V/50Hz	EZS158
250	S-50/HPS	120, 208, 240, 277/60Hz	EZS250
		480 60Hz	EZS255
		120, 277, 347/60Hz	EZS256
		220, 240V/50Hz	EZS258
400	S-51/HPS	120, 208, 240, 277/60Hz	EZS400
		480 60Hz	EZS405
		120, 277, 347/60Hz	EZS406
		220, 240V/50Hz	EZS408

^① HPS and MH assemblies may be ordered with the CEN (CENELEC) suffix; see page L164 for more information.

METAL HALIDE HOUSING GLOBE & GLOBE SUPPORT ASSEMBLIES ^①			
WATTS	ANSI LAMP TYPE	VOLTAGE	CATALOG NUMBER
70	M-98/MH	120, 208, 240, 277/60Hz	EZH070
		120, 277, 347V/60Hz	EZH076
		480 60Hz	EZH075
		220/240V/50Hz	EZH078
100	M-90/MH	120, 208, 240, 277/60Hz	EZH100
		120, 347V/60Hz	EZH106
		120, 220, 240V/50Hz	EZH108
		480 60Hz	EZH105
175	M-57/MH	120, 208, 240, 277/60Hz	EZH170
		480 60Hz	EZH175
		120, 277, 347V/60Hz	EZH176
		220, 240V/50Hz	EZH178
250	M-58/MH	120, 208, 240, 277/60Hz	EZH250
		480 60Hz	EZH255
		120, 277, 347V/60Hz	EZH256
		220, 240V/50Hz	EZH258
400	M-59/MH	120, 208, 240, 277/60Hz	EZH400
		480 60Hz	EZH405
		120, 277, 347V/60Hz	EZH406
		220, 240V/50Hz	EZH408

PULSE START HOUSING GLOBE & GLOBE SUPPORT ASSEMBLIES			
WATTS	ANSI LAMP TYPE	VOLTAGE	CATALOG NUMBER
175 ^②	M137/MHP	120, 208, 240, 277/60Hz	EZP170
		480	EZP175
		120, 277, 347V/60Hz	EZP176
		220, 240V/50 Hz	EZP178
250	M138/MHP	120, 208, 240, 277/60Hz	EZP250
		480	EZP255
		120, 277, 347V/60Hz	EZP256
		220, 240V/50Hz	EZP258
320	M132/MHP	120, 208, 240, 277/60Hz	EZP320
		480	EZP325
		120, 277, 347V/60Hz	EZP326
		220, 240V/50Hz	EZP328
350	M131/MHP	120, 208, 240, 277/60Hz	EZP350
		480	EZP355
		120, 277, 347V/60Hz	EZP356
		220, 240V/50Hz	EZP358
400	M135/MHP	120, 208, 240, 277/60Hz	EZP400
		480	EZP405
		120, 277, 347V/60Hz	EZP406
		220, 240V/50Hz	EZP408

^②For 150 Watt, change "7" to "5" in catalog number.
Example EZP150.

