



**Class I, Div. 1 & 2 Groups C,D**  
**Class I, Zone 1 & 2, Groups IIB,IIA**  
**Class I, Zone 1, AEx d IIB**  
**Class II, Div. 1 & 2, Groups E,F,G**  
**Class III, Div. 1 & 2**  
**Suitable for wet locations**  
**Marine**  
**NEMA 3, 4, 4X**  
**Factory Sealed**

Listed - File E10514 and E91793

Certified - File LR11713

### FEATURES-SPECIFICATIONS

## HOSTILELITE®

HOSTILELITE® EZ fixtures are now available with Pulse Start Metal Halide ballasts. Pulse Start systems provide higher and better maintained light output with longer life compared standard metal halide systems. Pulse start and standard Metal Halide lamps and ballasts are not interchangeable.

### Applications

HOSTILELITE® EZ Series mogul base fixtures are designed for installations where moisture, dirt, dust, corrosion and vibration may be present, or NEMA 3 and 4x areas where wind, water, snow or high ambients can be expected. They can be used in locations made hazardous due to the presence of flammable or explosive gases, vapors and combustible dusts as defined by the NEC.

Typical applications include classified areas such as paint manufacturing plants, ammunition facilities, oil and gas producing and refining plants, off-shore and dockside installations, tank farms, pipeline pumping stations and marine loading and fuel transfer terminals.

### Features

- Three light sources—High Pressure Sodium (50-400W), Metal Halide (70-400W) and Pulse Start Metal Halide (175-400W)
- HOSTILELITE® EZ fixtures are now available with Pulse Start Metal Halide ballasts
- Mounting choice—Pendant, ceiling, 25° stanchion or 90° wall mount, all with “wireless” design that allows fast, easy fixture installation or removal for

maintenance. See pages L196-197 for trunnion mounted fixtures


- Factory sealed—No external seal needed. Simply wire mounting cap and thread on fixture to install
- Corrosion resistant—Copper-free aluminum die cast construction. Baked powder epoxy finish, electrostatically applied. Exposed hardware is 316 grade stainless steel
- Accessories—Available with or without guard, standard dome or angle reflector
- Options—EZ Series fixtures can be specified with instant restart for HPS lamps, auxiliary quartz circuit, ballast

protector, and fuse kits.  
(See page L160 for details)

### Compliances

- UL-844 Electric Lighting Fixtures for use in Hazardous Locations
- UL Marine Type Electric Lighting Fixtures
- UL-1598 Standard for HID Lighting Fixtures
- CSA C22.2 no. 137-M1981 Electric Luminaires for use in Hazardous Locations
- CSA C22.2 no. 94-1976 Special purpose enclosure
- NEMA 3, 4, 4x, 7CD, 9EFG

### Catalog Number Logic



\*CEN (CENELEC) Approved option available on some models. See page L164 for more information.

Ⓢ Two eyebolts plus 12" of connecting chain included. Ⓢ 175,250 and 400W MH EXPORT ONLY (EISA LAW).

Ⓢ Consult factory for available lamp and voltage combinations.



## KILLARK®



Class I, Div. 1 & 2 Groups C,D  
 Class I, Zone 1 & 2, Groups IIB,IIA  
 Class I, Zone 1, AEx d IIB  
 Class II, Div. 1 & 2, Groups E,F,G  
 Class III, Div. 1 & 2  
 Suitable for wet locations  
 Marine  
 NEMA 3, 4, 4X  
 Factory Sealed

Listed - File E10514 and E91793 (Marine)

Certified - File LR11713

**FEATURES-SPECIFICATIONS**



EZ 50-400 WATT, HIGH PRESSURE SODIUM ① ④						
WATTS	ANSI LAMP	VOLTAGE @ 60Hz	CATALOG NUMBER			
			PENDANT 3/4"②	CEILING 3/4"②	WALL 3/4"②	STANCHION 1-1/4"③
50	S-68	120, 208, 240, 277	EZS050A2G	EZS050X2G	EZS050B2G	EZS050D4G
		120, 277, 347	—	—	—	—
		480	—	—	—	—
70	S-62	120, 208, 240, 277	EZS070A2G	EZS070X2G	EZS070B2G	EZS070D4G
		120, 277, 347	EZS076A2G	EZS076X2G	EZS076B2G	EZS076D4G
		480	EZS075A2G	EZS075X2G	EZS075B2G	EZS075D4G
100	S-54	120, 208, 240, 277	EZS100A2G	EZS100X2G	EZS100B2G	EZS100D4G
		120, 277, 347	EZS106A2G	EZS106X2G	EZS106B2G	EZS106D4G
		480	EZS105A2G	EZS105X2G	EZS105B2G	EZS105D4G
150	S-55	120, 208, 240, 277	EZS150A2G	EZS150X2G	EZS150B2G	EZS150D4G
		120, 277, 347	EZS156A2G	EZS156X2G	EZS156B2G	EZS156D4G
		480	EZS155A2G	EZS155X2G	EZS155B2G	EZS155D4G
250	S-50	120, 208, 240, 277	EZS250A2G	EZS250X2G	EZS250B2G	EZS250D4G
		120, 277, 347	EZS256A2G	EZS256X2G	EZS256B2G	EZS256D4G
		480	EZS255A2G	EZS255X2G	EZS255B2G	EZS255D4G
400	S-51	120, 208, 240, 277	EZS400A2G	EZS400X2G	EZS400B2G	EZS400D4G
		120, 277, 347	EZS406A2G	EZS406X2G	EZS406B2G	EZS406D4G
		480	EZS405A2G	EZS405X2G	EZS405B2G	EZS405D4G

① See Hazardous Location Application Data on pages L164-165 for specific suitabilityes.

② For 1 inch pendant, ceiling and wall hubs, substitute "3" for "2" in catalog number; example: EZS070A3G.

③ Stanchion conduit hub size supplied is 1-1/2" with 1-1/2" to 1-1/4" reducer for 1-1/4" mounting. (Refer to catalog logic).

④ Luminaire catalog numbers include guards. To order luminaire without guard, omit last letter "G" from catalog number.

NOTE: Reflectors must be ordered separately (see page L161).

All luminaires are designed for mounting with lamp in base up position.

