



EZS400A2-T - HID 400W Quadri-Volt High Pressure Sodium 3/4" Pendant with Guard Trunnion Mount

By Killark
Catalog # [EZS400A2-T](#)

HID 400W Quadri-Volt High Pressure Sodium 3/4" Pendant with Guard Trunnion Mount.



Features

- Trunnion mounted-Trunnion yoke of 316 grade stainless steel attaches via mounting blocks to fixture ballast housing
- Factory sealed-No external seal needed
- Corrosion resistant-Fixture of copper-free aluminum die cast construction. Baked powder epoxy finish, electro-statically applied. Exposed hardware of 316 grade stainless steel
- Accessories-Guards, reflectors and mounting hardware available. Must be ordered separately.

General

Finish Type	Powder Epoxy Paint
Lamp Type	Mogul Base
Light Source	High Pressure Sodium
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Mounting Type	Trunnion
Optic Type	Glass Globe - Clear
Series	EZ
UPC	783936097756

Electrical Ratings

Frequency Rating	60 Hz
Voltage Rating	Quad - 120/277/347/480 VAC
Wattage	400 W

Certifications and Compliance

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA
---------------------	---

Product Assets

[Certifications - EZ Series Luminaries CSA Certification](#)
[Customer Notices - Prop 65 Notice](#)
[Photometry - KIL_EZS40x](#)
[Photometry - KIL_EZS40x-S](#)
[Photometry - KIL_EZS40x-D](#)
[Photometry - KIL_EZS40x-A](#)



A proud member of the Hubbell Family.