



FF-90-3M - 90° 1" Iron Elbow, Female/Female

By Killark
Catalog # [FF-90-3M](#)

90° 1" Iron Elbow, Female/Female



Features

- Threaded for rigid conduit or IMC
- Smooth integral bushings to prevent damage to wires

Application

To change direction in rigid or IMC conduit systems.

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11716
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
UL File Number	E10514
Buy America(n) Qualified	Contact Manufacturer

Dimensions

Hub Size	1"
Length	3 in
Gross Weight with Packaging	0.93
Width	2 in
Height	3 in
Dimensions	3 in x 2 in x 3 in

General

Series	FF Series
Color	Glossy gray
Type	90° Elbow
Material	Iron
Finish Type	Powder Epoxy Paint
UPC	783936170251

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)