

Switches and Lighting Control, Fluorescent
Starter, 14-15-20W

By Hubbell Wiring Device-Kellems
Catalog # [FS2](#)

Switches and Lighting Control, Fluorescent Starter, 14-15-20W



Features

- Rugged construction
- Operates over a wide temperature range
- Neostart lights in dual lamp circuit uniformly and quickly

Specifications

Standards - RoHS Compliance	CM
Status	
EU RoHS Indicator	Yes
Industry Standard(s)	UL Listed

Current

Frequency Rating	60 Hz
Voltage Rating	Determined by the ballasts kV
Wattage	14, 15 and 20 Watt Lamps

Dimensions

Length	1.5 in
Height	0.7 in
Width	0.7 in
Dimensions	1.5 in x 0.7 in x 0.7 in

General

Color	Gray
OEM Brand Name	Hubbell Wiring Device-Kellems
Lamp Type	Fluorescent
Specifications	• Product Type - Fluorescent Starters • Starter Wattage - 14, 15 and 20 watt lamps
UPC	783585750002
Material - Mounting Hardware	Twist-In

Logistics

Pallet Quantity	36000
Carton Quantity	25

Operational

Start Type	Neo Start
------------	-----------

Product Assets

- [Catalog \[English\]](#)
[Catalog Page \[English\]](#)