



## FXCS-1S2A1-MI - FXCS Series, Seal-XM, Iron Dead-End Maintained Contact 2-Position Selector Switch Ctrl Stn, Off - On/Blank, Hub Size 1/2", 1NO/1NC

By Killark  
Catalog # [FXCS-1S2A1-MI](#)



FXCS Series - Seal-XM - Iron Dead-End Maintained Contact 2-Position Selector Switch Control Station - Factory Sealed - "Off - On"/Blank Nameplate - Hub Size 1/2 Inch - 1NO/1NC Contact Rating

### Features

- Incorporates Factory Sealed Universal contact blocks and GOB3 LED pilot light devices.
- External sealing fittings typically not required, reducing installation time and cost.
- No seal plate between the electrical device and back box allows direct wiring to contact terminals.
- NEMA 3 weatherproof.
- Grounding boss supplied in the splice box.
- Sold as a complete unit.
- Standard finish is a gray epoxy powder baked on for ultimate corrosion resistance.
- More wiring room in back box.

### Application

SEAL-XM Series is used to prevent the igniting of external hazardous atmospheres by the enclosed arcing devices in such areas as: hazardous locations due to the presence of flammable gases or vapors, combustible dusts or easily ignitable fibers or flyings

### Specifications

Hazardous Rating(s)	<ul style="list-style-type: none"> <li>• Class I, Divisions 1 &amp; 2, Groups C, D</li> <li>• Class I, Zones 1 &amp; 2, Groups IIB, IIA</li> <li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li> <li>• Class III, Divisions 1 &amp; 2</li> </ul>
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3
CSA File Number	LR11714, 2493125

Buy America(n) Qualified

Contact Manufacturer

### Configuration

Back Box Type	FXB
Hub Pattern	Dead-End

### Current

Amperage Rating	10 A
Frequency Rating	50/60 Hz

### Dimensions

Depth	4.84 in
Hub Size	1/2"

### General

Type	Factory Sealed
Series	FXCS Seal-XM Series
UPC	783936001272
Color	Black

### Logistics

Factory Sealed	Factory Sealed
----------------	----------------

### Operational

Action	Maintained
Actuator	2 Position Selector Switch

### Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)