



FXCS Series - Dead-End 2-Position Spring Returned Standard Selector Switch- Return to Left from Right- 1/2" Hub- 1NO/1NC Contact Rating

By Killark

Catalog # [FXCS-1S2L3F](#)

FXCS Series - Aluminum Dead-End 2-Position Spring Returned Standard Selector Switch- Return to Left from Right- 1/2" Hub- 1NO/1NC Contact Rating



Features

- Eliminates external sealing requirements.
- Lower installation cost.
- NEMA 3 weatherproof.
- Color coded wiring with more wiring space for easier field installation.
- Stainless steel captive screws for cover assembly.
- Lockout accessory available must be factory installed.
- Ground boss for grounding in the splice box.
- Device bodies and covers are copper-free cast aluminum alloy.
- Push button, selector switches and pilot light bodies are copper-free aluminum.
- Operating shaft in both push buttons and selector switches are stainless steel.

Application

SEAL-X Series is used to prevent the igniting of external hazardous atmospheres by the enclosed arcing devices in such areas as: hazardous locations due to the presence of flammable gases or vapors, combustible dusts or easily ignitable fibers or flyings

Specifications


Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3
UL File Number	E53360, E12379
CSA File Number	LR11714, LR11712
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Poles	1
-----------------	---

Configuration

Back Box Type	FXB
Hub Pattern	Dead-End



Current

Contact Rating	• 60A INRUSH @ 120 VAC • 30A INRUSH @ 240 VAC • 15A INRUSH @ 480 VAC • 12A INRUSH @ 600 VAC • 6A BREAKING @ 120 VAC • 3A BREAKING @ 240 VAC • 1.5A BREAKING @ 480 VAC • 1.2A BREAKING @ 600 VAC • 10A CARRYING @ 120 VAC • 10A CARRYING @ 240 VAC • 10A CARRYING @ 480 VAC
Amperage Rating	10 A
Frequency Rating	50/60 Hz

Dimensions

Gross Weight with Packaging	4.5
Depth	5.62 in
Hub Size	1/2"
Width	6 in
Height	4.38 in
Length	6.63 in
Dimensions	6.63 in x 6 in x 4.38 in

General

Type	Factory Sealed
Series	FXCS Series
UPC	783936201061
Color	Black

Logistics

Factory Sealed	Factory Sealed
----------------	----------------

Operational

Action	Momentary
Actuator	2 Position Selector Switch

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)
- [Installation Manual \[French\]](#)