



FXCS-1S3L6G-M - FXCS Series, Seal-XM, AL Dead-End 3-Position Spring Standard Selector Switch, Return Center from Right, 1/2" Hub, 2NO Contact Rating

By Killark
Catalog # [FXCS-1S3L6G-M](#)

FXCS Series - Seal-XM - Aluminum Dead-End 3-Position Spring Returned Standard Selector Switch - Return to Center from Right - Factory Sealed - 1/2" Hub - 2NO Contact Rating

Features

- Incorporates Factory Sealed Universal contact blocks and GOB3 LED pilot light devices.
- External sealing fittings typically not required, reducing installation time and cost.
- No seal plate between the electrical device and back box allows direct wiring to contact terminals.
- NEMA 3 weatherproof.
- Grounding boss supplied in the splice box.
- Sold as a complete unit.
- Standard finish is a gray epoxy powder baked on for ultimate corrosion resistance.
- More wiring room in back box.

Application

SEAL-XM Series is used to prevent the igniting of external hazardous atmospheres by the enclosed arcing devices in such areas as: hazardous locations due to the presence of flammable gases or vapors, combustible dusts or easily ignitable fibers or flyings

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3
CSA File Number	LR11714, 2493125



Buy America(n) Qualified	Contact Manufacturer
Configuration	
Back Box Type	FXB
Hub Pattern	Dead-End
Current	
Amperage Rating	10 A
Frequency Rating	50/60 Hz
Dimensions	
Depth	4.84 in
Hub Size	1/2"
General	
Type	Factory Sealed
Series	FXCS Seal-XM Series
UPC	783936001425
Color	Black
Logistics	
Factory Sealed	Factory Sealed
Operational	
Action	Momentary Right
Actuator	3 Position Selector Switch
Product Assets	
Catalog [English]	
Installation Manual [English]	