



FXCS-2K3M6G32A-MBI - FXCS Series,
Seal-XM, Iron Dead-End 3-Position Spring
Returned Selector Switch; Return to Ctr,
3/4" Hub, 2NO Contact Rating

By Killark
Catalog # FXCS-2K3M6G32A-MBI

FXCS Series - Seal-XM - Iron Dead-End 3-Position Spring
Returned Keyed Alike Selector Switch- Return to Center From
Right Or Left- 3/4" Hub- 2NO Contact Rating- Group B Rated

Features

- Incorporates Factory Sealed Universal contact blocks and GOB3 LED pilot light devices.
- External sealing fittings typically not required, reducing installation time and cost.
- No seal plate between the electrical device and back box allows direct wiring to contact terminals.
- NEMA 3 weatherproof.
- Grounding boss supplied in the splice box.
- Sold as a complete unit.
- Standard finish is a gray epoxy powder baked on for ultimate corrosion resistance.
- More wiring room in back box.

Application

SEAL-XM Series is used to prevent the igniting of external hazardous atmospheres by the enclosed arcing devices in such areas as: hazardous locations due to the presence of flammable gases or vapors, combustible dusts or easily ignitable fibers or flyings

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3
CSA File Number	LR11714, 2493125



Buy America(n) Qualified Contact Manufacturer

Configuration

Back Box Type	FXB
Hub Pattern	Dead-End

Current

Amperage Rating	10 A
Frequency Rating	50/60 Hz

Dimensions

Depth	5.28 in
Hub Size	3/4"

General

Type	Factory Sealed
Series	FXCS Seal-XM Series
UPC	783936006536
Color	Black

Logistics

Factory Sealed	Factory Sealed
----------------	----------------

Operational

Action	Momentary Left & Right
Actuator	3 Position Key Selector Switch

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)