



GEBL-5 - 1-1/2" GEB Outlet Body, L Type, Aluminum

By Killark
Catalog # [GEBL-5](#)

1-1/2" GEB Outlet Body, L Type, Aluminum

Features

- Suitable for NEMA 4X applications
- Integral mounting lugs
- Green ground screw standard
- External cover thread on body plus smooth integral hub bushing protects conductor insulation when pulling
- Taper threaded hubs provide ground continuity
- External threaded body for additional wiring room
- Includes cover and gasket

Application

Conduit boxes installed in conduit systems within hazardous areas to: protect conductors in threaded rigid conduit, act as pull and splice boxes, interconnect lengths of conduit, change conduit direction, and provide access to conductors for maintenance and future system changes.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
UL File Number	E10514



CSA File Number	LR11716
Buy America(n) Qualified	Contact Manufacturer

Configuration

Hub Pattern	L
-------------	---

Dimensions

Gross Weight with Packaging	2.8
Hub Size	1-1/2"
Width	8.38 in
Height	4.13 in
Length	10.31 in
Dimensions	10.31 in x 8.38 in x 4.13 in

General

Type	Outlet Body With Cover
Series	GE Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
UPC	783936114774
Color	Gray

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)