



GECET-3M - 1" GEC Outlet Body, E-Type, Iron

By Killark
Catalog # [GECET-3M](#)

1" GEC Outlet Body, E-Type, Iron

Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

Application

Conduit boxes installed in conduit systems within hazardous areas to: protect conductors in threaded rigid conduit, act as pull and splice boxes, interconnect lengths of conduit, change conduit direction, and provide access to conductors for maintenance and future system changes.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA
EU RoHS Indicator	Contact Manufacturer



UL File Number	E10514
CSA File Number	LR11716
Buy America(n) Qualified	Contact Manufacturer

Configuration

Hub Pattern	E
-------------	---

Dimensions

Gross Weight with Packaging	3.26
Hub Size	1"
Width	5.875 in
Height	4.25 in
Length	6.125 in
Dimensions	6.125 in x 5.875 in x 4.25 in

General

Type	Outlet Body With Cover
Series	GE Series
Material	Iron
Finish Type	Powder Epoxy Paint
UPC	783936210803
Color	Gray

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)