



GEJLBT-6 - 2" GEJ Outlet Body LB Type, Aluminum

By Killark
Catalog # [GEJLBT-6](#)

2" GEJ Outlet Body LB Type, Aluminum

Features

- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Cover furnished with box.
- Weather-resistant finish.
- Green ground screw standard.

Application

Conduit boxes installed in conduit systems within hazardous areas to: protect conductors in threaded rigid conduit, act as pull and splice boxes, interconnect lengths of conduit, change conduit direction, and provide access to conductors for maintenance and future system changes.

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR11716
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Group C (if sealed within 18"), D • Class I, Zones 1 & 2, Group IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2



UL File Number	E10514
Buy America(n) Qualified	Contact Manufacturer

Configuration

Hub Pattern	LB
-------------	----

Dimensions

Hub Size	2"
Length	8.13 in
Gross Weight with Packaging	4.68
Width	5.81 in
Height	6.75 in
Dimensions	8.13 in x 5.81 in x 6.75 in

General

Series	GE Series
Color	Gray
Type	Outlet Body With Cover
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
UPC	783936211121

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)