



GEJLBT-6M - 2" GEJ Outlet Body LB Type, Iron

By Killark
Catalog # [GEJLBT-6M](#)

2" GEJ Outlet Body LB Type, Iron



Features

- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Cover furnished with box.
- Weather-resistant finish.
- Green ground screw standard.

Application

Conduit boxes installed in conduit systems within hazardous areas to: protect conductors in threaded rigid conduit, act as pull and splice boxes, interconnect lengths of conduit, change conduit direction, and provide access to conductors for maintenance and future system changes.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Group C (if sealed within 18"), D • Class I, Zones 1 & 2, Group IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
---------------------	--

EU RoHS Indicator	Contact Manufacturer
UL File Number	E10514
CSA File Number	LR11716
Buy America(n) Qualified	Contact Manufacturer

Configuration

Hub Pattern	LB
-------------	----

Dimensions

Gross Weight with Packaging	11.02
Hub Size	2"
Width	6 in
Height	7.75 in
Length	8.375 in
Dimensions	8.375 in x 6 in x 7.75 in

General

Type	Outlet Body With Cover
Series	GE Series
Material	Iron
Finish Type	Powder Epoxy Paint
UPC	783936211176
Color	Gray

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)