



## GESCT-4 - 1-1/4" GES Outlet Body C-Type, Aluminum

By Killark  
Catalog # [GESCT-4](#)

1-1/4" GES Outlet Body C-Type, Aluminum

### Features

- Water shedding cover – suitable for wet locations when mounted in upright position.
- External cover threads on body protecting conductors from damage during pulling.
- No pinching of conductors during cover installation.
- Taper threaded hubs to provide ground continuity.
- Smooth integral hub bushing to protect conductor insulation when pulling.
- Internally threaded cover openings for additional wiring room.
- Covers furnished with boxes.
- Weather-resistant finish.
- Green ground screw standard.

### Application

Conduit boxes installed in conduit systems within hazardous areas to: protect conductors in threaded rigid conduit, act as pull and splice boxes, interconnect lengths of conduit, change conduit direction, and provide access to conductors for maintenance and future system changes.

### Specifications

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Divisions 1 &amp; 2, Group D</li><li>• Class I, Zones 1 &amp; 2, Group IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups E, F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul>
---------------------	--



EU RoHS Indicator	Contact Manufacturer
UL File Number	E10514
CSA File Number	LR11716
Buy America(n) Qualified	Contact Manufacturer

### Configuration

Hub Pattern	C
-------------	---

### Dimensions

Gross Weight with Packaging	2.98
Hub Size	1-1/4"
Width	6 in
Height	6.75 in
Length	8.25 in
Dimensions	8.25 in x 6 in x 6.75 in

### General

Type	Outlet Body With Cover
Series	GE Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
UPC	783936210308
Color	Gray

### Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)